



GFCI receptacles from the radiant® Collection self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. Meeting National Electrical Code requirements for ground fault protection, GFCI receptacles make it easier to recognize and fix trips right where they happen – no more confusion at the breaker box. Also including tamper and weather\* resistance, this model was designed for use in outdoor spaces. Maximize safety, in style, with GFCI protection featuring the sleek, clean lines of radiant. 20A outlets are ideal for use with larger appliances and in commercial settings, as well as to meet regional requirements (Chicago, Canada). GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately. Spec-Grade devices are engineered to meet federal specifications for use in commercial installations.

## Features & Benefits

- Protects against shock caused by ground-fault occurrences. Unlike breaker alternatives, GFCI receptacles make it easier to fix trips with a reset button right on the device.
- Conducts an industry-leading automatic self-test every 3 seconds. If the device ever fails, the indicator light flashes to signal it should be replaced.
- Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the outlet is disconnected.
- Extends GFCI protection to "downstream" outlets when used with feed-thru wiring configuration. Note: Will cut power to face and downstream outlets if wired incorrectly.
- Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection
- Replaces any standard receptacle with ease, in as little as 10 minutes.
- Features durable, high-impact resistant thermoplastic construction.
- More color options available to fit any style, including finishes to match current hardware and lighting trends.
- Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	Country Of Origin	China
Number of Receptacles	2	Outlet Type	GFCI, Outdoor, Residential, Self-Test, Weather-Resistant
Application Sector	Residential/Commercial	Standard	cULus, UL Listed, FSUL
Warranty Type	1-Year Limited Warranty	Type	Outlet

### Dimensions

Product Width US	1.73 in	Product Depth US	1.13 in
Product Height US	4.2 in		

---

## Listing Agencies / 3rd Party Agencies

---

cULus Listed Yes

---

## Additional Information

---

Product Environmental Profile Yes

---

## Technical Information

---

Interrupt Rating	4 A	Frequency Rating	60 Hz
------------------	-----	------------------	-------

---

Trip Range	5±1 mA	Number of Gangs	1
------------	--------	-----------------	---

---

Amperage	20 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

---

Indoor/Outdoor	Outdoor	NEMA Configuration Code	5-20R
----------------	---------	-------------------------	-------

---

Mounting Type	Box	Voltage	125.0 V
---------------	-----	---------	---------

---

Environmental Conditions	95% Humidity, UL 94 V2
--------------------------	------------------------

---