




Ortronics  
**Infinium Keyed LC Splice-On Connector (SOC) For 900 Micron Fiber, 9/125 Single-Mode OS2 50 Pack Green**  
Part No. 205KKF9SD-09-M



Legrand keyed LC fiber solutions provide a simple and convenient way to physically prevent the user from making an unauthorized connection by blocking access to specific optical ports, whether they are at a workstation outlet or in a telecommunications room or data center. This is particularly important for government, finance, military and other facilities where multiple networks having different security level access requirements may be co-located.

## Features & Benefits

|   |   |
|---|---|
| 12 color/key configurations available   | 50/125 microns and 9/125 microns laser-optimized fiber types available    |
| LC Keyed cadapters prevent improper connection of separate networks with common access points | Each LC secure adapter will mate only with same-color LC secure connector |
| High quality 1.25 mm zirconia ferrules used   | Internal keying feature prevents tampering                                |
| High quality 1.25 mm zirconia ferrules used   | 1.6 in boot protects the splice for easy cable management                 |
| The solution to managing multiple networks with reduced risks                                 |   |

## Specifications

### General Info

|                   |               |            |              |
|-------------------|---------------|------------|--------------|
| Product Line      | Ortronics     | UPC Number | 662875034001 |
| Country Of Origin | United States | Type       | Connector    |

### Dimensions

|                   |          |                  |         |
|-------------------|----------|------------------|---------|
| Product Width US  | 0.236 in | Product Depth US | 3.65 in |
| Product Height US | 0.409 in |                  |         |

### Technical Information

|              |                                     |                    |              |
|--------------|-------------------------------------|--------------------|--------------|
| Service Life | < 0.2dB typical change, 500 matings | Temperature Rating | -40° - 75° C |
| Fiber Size   | 9/125                               |                    |              |