




Legrand

radiant® Spec-Grade 20A Tamper-Resistant Self-Test GFCI Receptacle
Part No. 2097TRRED



GFCI receptacles from the radiant® Collection self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. Meeting National Electrical Code requirements for ground fault protection, GFCI receptacles make it easier to recognize and fix trips right where they happen – no more confusion at the breaker box. 20A outlets are ideal for use with larger appliances and in commercial settings, as well as to meet regional requirements (Chicago, Canada). GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately. Spec-Grade devices are engineered to meet federal specifications for use in commercial installations.

Features & Benefits

Part of the radiant: collection

Protects children: patented shutter system helps prevent improper insertion of foreign objects meeting National Electrical Code: Tamper-Resistant requirements

Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the trip indicator light (red LED) flashes to signal that the GFCI should be replaced

Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected

Thinner than competitors' GFCI Receptacles: leaves more room for wires in the box

Feed-thru wiring configuration allows GFCI to protect downstream receptacles

Meets 2015 UL requirements.

Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly

Side or internal screw-pressure-plate back wire with #10-#14 AWG solid or stranded copper wire and two back wire holes per terminal

Mounting screws are shipped captive in the device and wall plate for easier installation

Dual-direction test and reset button colors match the device face

Supplied with matching TP wall plate (except NI and DB models)

10kA short circuit rating

20 Amp feed-thru capacity

Specifications

General Info

Color Red

UPC Number 785007035681

Country Of Origin China

Product Line Pass & Seymour

Application Sector Residential/Commercial

Standard cULus, UL Listed, FSUL

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Additional Information

Product Environmental Profile Yes

Technical Information

Number of Poles	Double Pole
Voltage	125 V
Trip Range	4 to 6 mA
Connection	Back and Side Wire
Frequency Rating	60 Hz
Interrupt Rating	4 A
Environmental Conditions	95% Humidity, UL 94 V2
