



6' Steel Plugmold Multioutlet Strip with 3 duplex receptacles spaced at 24", GB

Features & Benefits

Steel Raceway. Provides superior strength for any dry location installation with greater wire capacity than V2000.

Ivory ScuffCoat finish. Durable scratch resistant finish.

Removable cover. Allows easy access to wiring for changes or additions.

Full range of fittings. Provides a complete wiring solution.

Single-and-dual-gang boxes. Wire devices into the raceway system or protect a Plugmold® strip with a surge or GFCI device.

Factory wired Plugmold® sections available in 3', 5', and 6' lengths with 20A, 120V receptacles. Ideal for short runs requiring additional outlets in electrically busy areas.

Single or alternating circuit. Meets virtually any circuit requirement.

Choice of receptacle spacing. Center spacing between receptacles of 6", 12" and 18".

Simplex receptacle. More spacing options available.

Duplex receptacle. Aesthetically pleasing, functional 20A duplex for the 24S (2400) Series.

Customization available. All products can be modified to accommodate virtually any application.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776165180
Country Of Origin	United States	Number of Receptacles	3

Application Sector		Commercial	Standard	cULus Listed Base & Blank Cover: File E4376 Guide RJBT. Multioutlet Assemblies: File E15191 Guide PVGT. Fittings: File E41751 Guide RJPR. Base & Blank Cover& Plugmold Series w/Snapcoil Harness: Meets Article 386 of NEC. Meets Section 12-3032 of CEC. Plugmold Wired Sections: Meets Article 380 of NEC. Meets Section 12-3032 of CEC.
Type		Plugmold		
Listing Agencies / 3rd Party Agencies				
cULus ListingNumber		E15191	cULus Listed	Yes
Buy American Act Compliance				
NAFTA		Yes		
Additional Information				
RoHS Conformant		Yes		
Technical Information				
Amperage		15 A	Enclosure Type	Steel
Voltage		125.0 V	Environmental Conditions	Dry interior locations