



SteriGuard Anti-Microbial Wiring Devices provide excellent protection against the growth of microbes on all surfaces. Independent testing proves the ability of these devices to inhibit the growth of Escherichia coli, Gram (-) and Staphylococcus aureus, Gram (+) providing long lasting benefits to manufacturers beyond conventional cleaning methods. Rated watertight for 1,500 psi high-pressure

Features & Benefits

UL and CSA Listed

NSF (National Sanitation Foundation) Certified

Patent Pending

Anti-microbial Additives Embedded in polymer and inhibits Growth of Bacteria, Molds, Mildews and Fungi

Anti-microbial Additive Resistant to Scuffing and Cleaning

Escherichia (E.Coli): - Log reduction greater than 4.8, reduces surface bacteria by greater than 99.99%

Staphylococcus (Staph), MRSA: - Log Reduction greater than 4.3, reduces surface bacteria by greater than 99.97%

Salmonella : Log Reduction Greater Than 3.6, reduces surface bacteria by Greater Than 99.97%

RoHS Compliant (Non-Halogenated)

Independently tested and Certified to JIS Z2801 standards

Resistant to High Pressure Hose-down applications

Tongue & Groove Environmental Sealing

Keyed Body and Cover for Alignment

NEMA Type 4, 4x, 6, 6P and IP67 Protection

SteriGuard: Anti-microbial Wiring Devices are ideal for a wide range of applications including food and beverage preparation, procession, & packaging: agriculture, pharmaceutical, and health care.

Specifications

General Info

| | | | |
|-------------------|----------------|----------|-----------------------|
| Product Line | Pass & Seymour | Color | Yellow |
| Country Of Origin | United States | Standard | UL Listed, CSA Listed |

Dimensions

| | | | |
|------------------|---------|------------------|---------|
| Product Width US | 1.85 in | Product Depth US | 4.03 in |
|------------------|---------|------------------|---------|

| | |
|-------------------|---------|
| Product Height US | 1.85 in |
|-------------------|---------|

Listing Agencies / 3rd Party Agencies

| | |
|------------|-----|
| CSA Listed | Yes |
|------------|-----|

Technical Information

| | | | |
|-------|--------|-----------------|---|
| Phase | Single | Number of Wires | 3 |
|-------|--------|-----------------|---|

| | | | |
|----------|------|-----------------|-------------|
| Amperage | 15 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

| | | | |
|-----------|-------------|---------|---------|
| Wire Size | 18 - 12 AWG | Voltage | 125.0 V |
|-----------|-------------|---------|---------|

| | |
|--------------------------|--|
| Environmental Conditions | Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized |
|--------------------------|--|
