



Wiremold
24S7218IGX99IV Steel Plugmold® Multioutlet Strip
Part No. 24S7218IGX99IV



6' Steel Plugmold Multioutlet Strip with 4 duplex receptacles spaced at 18", IG

Features & Benefits

Steel Raceway. Provides superior strength for any dry location installation with greater wire capacity than V2000.

Ivory ScuffCoat finish. Durable scratch resistant finish.

Removable cover. Allows easy access to wiring for changes or additions.

Full range of fittings. Provides a complete wiring solution.

Single-and-dual-gang boxes. Wire devices into the raceway system or protect a Plugmold® strip with a surge or GFCI device.

Factory wired Plugmold® sections available in 3', 5', and 6' lengths with 20A, 120V receptacles. Ideal for short runs requiring additional outlets in electrically busy areas.

Single or alternating circuit. Meets virtually any circuit requirement.

Choice of receptacle spacing. Center spacing between receptacles of 6", 12" and 18".

Simplex receptacle. More spacing options available.

Duplex receptacle. Aesthetically pleasing, functional 20A duplex for the 24S (2400) Series.

Customization available. All products can be modified to accommodate virtually any application.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776165197
Country Of Origin	United States	Number of Receptacles	4

Application Sector	Commercial	Standard	cULus Listed Base & Blank Cover: File E4376 Guide RJBT. Multioutlet Assemblies: File E15191 Guide PVGT. Fittings: File E41751 Guide RJPR. Base & Blank Cover& Plugmold Series w/Snapcoil Harness: Meets Article 386 of NEC. Meets Section 12-3032 of CEC. Plugmold Wired Sections: Meets Article 380 of NEC. Meets Section 12-3032 of CEC.
Type	Plugmold		
Dimensions			
Product Weight US	5.4 lb		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E15191	cULus Listed	Yes
Trade Programs			
USMCA	Yes		
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Amperage	15 A	Enclosure Type	Steel
Voltage	125.0 V	Environmental Conditions	Dry interior locations