

Single-Pole, Back and Side-Wire, Decorator Switch, 15A, 120/277V



Features & Benefits

Impact-resistant polycarb back body and frame.

Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.

Terminals made of high conductivity brass and serrated for maximum wire gripping.

Integral auto-ground clip for positive ground to metal boxes.

All terminal screws backed out, ready-to-install.

Cushioned thermoplastic paddle assures smooth, quiet, long term operation.

Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire.

Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.

Tri-drive ground, terminal, and mounting screws.

For covering patents, see

Specifications

General Info

| | | | |
|--------------------|------------------------|---------------------|-------------------------|
| Product Line | Pass & Seymour | Color | Gray |
| Finish | Matte | UPC Number | 785007539028 |
| Country Of Origin | Mexico | Features | Decorator Style |
| Switch Type | Paddle | Number of Switches | 1 |
| Application Sector | Commercial, Industrial | Wall Plate Included | No |
| Standard | UL 20 | Warranty Type | 1-Year Limited Warranty |

| | | | |
|---------------------------------------|----------------------|---------------------------|--|
| Type | Decorator, Switch | | |
| Dimensions | | | |
| Product Width US | 1.3 in | Product Depth US | 1.03 in |
| Product Height US | 4.2 in | | |
| Listing Agencies / 3rd Party Agencies | | | |
| CSA Listed | Yes | cULus Listed | Yes |
| CSA File Number | 17446 | | |
| Technical Information | | | |
| Operating Temperature Min | -4 °F | Load Rating | 15 A @ 120/277 VAC |
| Connection Location | Back and Side | Horsepower Rating | 1/2 HP @ 120 VAC, 2 HP @ 240 VAC |
| Terminal Accommodation | #14 AWG - #10 AWG | Operating Temperature Max | 140 °F |
| Number of Gangs | 1 | Amperage | 15 A |
| Number of Poles | Single Pole | Requires Neutral Wire | No |
| Indoor/Outdoor | Indoor | Mounting Type | Wall Box |
| Operating Temperature | -20°-60°C, -4°-140°F | Wire Connection Type | Screw Terminals |
| Voltage | 120 VAC, 277 VAC | Load Type | CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon |