



Heavy-Duty Decorator Spec Grade Duplex Receptacle Side Wire 15A 125V

Features & Benefits

Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.

One-piece, brass, triple-wipe power contacts for lasting retention.

Heavy-duty compact design for easier installation and long lasting performance.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Impact-resistant nylon face.

Terminal compartments isolated from each other for positive conductor containment.

Tri-drive terminal and mounting screws.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

| | | | |
|-------------------|--------------------|-----------------------|------------|
| Product Line | Pass & Seymour | Color | Gray |
| Country Of Origin | Mexico | Number of Receptacles | 2 |
| Outlet Type | Commercial, Indoor | Application Sector | Commercial |
| Standard | UL498, cUL CSA | Type | Outlet |

Dimensions

| | | | |
|-------------------|----------|------------------|----------|
| Product Width US | 1.322 in | Product Depth US | 0.833 in |
| Product Height US | 2.635 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|---------------------|--------------------------|--------------------------|-----------------------|
| Dielectric Strength | Withstands 2000V minimum | Connection | Side wire |
| Number of Wires | 3 | Temperature Rating | -40° - 60° C |
| Amperage | 15 A | Number of Poles | Double Pole |
| Wire Size | 14 - 10 AWG | Indoor/Outdoor | Indoor |
| Voltage | 125.0 V | Environmental Conditions | Flammability: UL94 V2 |
