



Pass and Seymour  
**15A 125V Heavy Duty Decorator Spec Grade Single Receptacles, Back and Side Wire, White**  
Part No. 26261W



Heavy-Duty Decorator Spec Grade Single Receptacle Back and Side-Wire 15A 125V

## Features & Benefits

Corrosion-resistant, plated wraparound steel strap locked into assembly to prohibit strap from bending away from body.

Heavy-duty compact design for easier installation and long lasting performance.

Impact-resistant nylon face.

Side and internal screw-pressure-plateback wire accepts #14 : #10 AWG solid or stranded wire.

Tri-drive terminal and mounting screws.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.  
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

One-piece, brass, triple-wipe power contacts for lasting retention.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Terminal compartments isolated from each other for positive conductor containment.

All devices fit standard #26 opening wall plate.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
UPC Number	785007784695	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL498, cUL CSA, FEDSPEC

---

### Dimensions

Product Width US	1.322 in	Product Depth US	1.188 in
Product Length US	2.635 in		

### Listing Agencies / 3rd Party Agencies

cUL ListingNumber	140596	cUL Listed	Yes
-------------------	--------	------------	-----

### Technical Information

Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
Number of Wires	3	Temperature Rating	-40° - 60° C
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Environmental Conditions	Flammability: UL94 V2