



Pass and Seymour  
15A 250V Heavy Duty Specification Grade Single Decorator Receptacles, White  
Part No. 26661W

Heavy-Duty Decorator Spec Grade Single Receptacle Back and Side-Wire  
15A 250V



## Features & Benefits

- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.
- Heavy-duty compact design for easier installation and long lasting performance.
- Impact-resistant nylon face.
- Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire.
- Tri-drive terminal and mounting screws.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
- Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact
- One-piece, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Terminal compartments isolated from each other for positive conductor containment.
- All devices fit standard #26 opening wall plate.
- Auto-ground clip assures positive ground.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
UPC Number	785007786064	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL498, cUL CSA, FEDSPEC

Dimensions

Product Width US	1.322 in	Product Depth US	1.188 in
Product Length US	2.635 in		

Listing Agencies / 3rd Party Agencies

cUL ListingNumber	140596	cUL Listed	Yes
-------------------	--------	------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
Number of Wires	3	Temperature Rating	-40° - 60° C
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Environmental Conditions	Flammability: UL94 V2