



Pass and Seymour

Heavy-Duty Decorator Spec Grade Single Receptacles, Back & Side Wire, 20A, 125V, Black
Part No. 26361BK

Heavy-Duty Decorator Spec Grade Single Receptacle Back & Side Wire 20amp 125volt Ivory



Features & Benefits

Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.

One-piece, brass, triple-wipe power contacts for lasting retention.

Heavy-duty compact design for easier installation and long lasting performance.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Impact-resistant nylon face.

Terminal compartments isolated from each other for positive conductor containment.

Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire.

All devices fit standard #26 opening wall plate.

Tri-drive terminal and mounting screws.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Color	Black	UPC Number	785007785432
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Commercial	Standard	UL498, cUL CSA

Listing Agencies / 3rd Party Agencies

cUL Listed	Yes	cUL ListingNumber	140596
------------	-----	-------------------	--------

Technical Information

Number of Poles	Double Pole	Voltage	125 V
Connection	Back and side wire	Dielectric Strength	Withstands 2000V minimum
Temperature Rating	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact	Wire Size	#14 - #10

Number of
Wires 3

Environmental Conditions

Flammability: UL94 V2
