



## Legrand

Heavy-Duty Decorator Spec Grade Receptacles, Back & Side Wire, 20A, 250V, Black

Part No. 26852BK



Heavy-Duty Decorator Spec Grade Duplex Receptacle Back & Side Wire 20amp 250volt Brown

### Features & Benefits

Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.

Heavy-duty compact design for easier installation and long lasting performance.

Impact-resistant nylon face.

Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire.

Tri-drive terminal and mounting screws.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

One-piece, brass, triple-wipe power contacts for lasting retention.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Terminal compartments isolated from each other for positive conductor containment.

All devices fit standard #26 opening wall plate.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

### Specifications

#### General Info

Color Black

UPC Number 785007786378

Country Of Origin Mexico

Product Line Pass & Seymour

Application Sector Commercial

Standard UL498, cUL CSA

#### Listing Agencies / 3rd Party Agencies

cULus Listed Yes

cULus ListingNumber 140596

#### Technical Information

Number of Poles Double Pole

---

<b>Voltage</b>	250 V
----------------	-------

---

<b>Connection</b>	Back and side wire
-------------------	--------------------

---

<b>Dielectric Strength</b>	Withstands 2000V minimum
----------------------------	--------------------------

---

<b>Temperature Rating</b>	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact
---------------------------	---

---

<b>Wire Size</b>	#14 - #10
------------------	-----------

---

<b>Number of Wires</b>	3
------------------------	---

---

<b>Environmental Conditions</b>	Flammability: UL94 V2
---------------------------------	-----------------------

---