



Heavy-Duty Decorator Spec Grade Single Receptacle Back and Side-Wire 20A 125V



Features & Benefits

- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.
- Heavy-duty compact design for easier installation and long lasting performance.
- Impact-resistant nylon face.
- Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire.
- Tri-drive terminal and mounting screws.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- One-piece, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Terminal compartments isolated from each other for positive conductor containment.
- All devices fit standard #26 opening wall plate.
- Auto-ground clip assures positive ground.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.  
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

|                   |                |                    |            |
|-------------------|----------------|--------------------|------------|
| Product Line      | Pass & Seymour | Color              | Black      |
| Country Of Origin | Mexico         | Application Sector | Commercial |
| Standard          | UL498, cUL CSA |                    |            |

Dimensions

|                   |          |                  |          |
|-------------------|----------|------------------|----------|
| Product Width US  | 1.322 in | Product Depth US | 1.188 in |
| Product Length US | 2.635 in |                  |          |

Listing Agencies / 3rd Party Agencies

|                   |        |            |     |
|-------------------|--------|------------|-----|
| cUL ListingNumber | 140596 | cUL Listed | Yes |
|-------------------|--------|------------|-----|

Technical Information

|                          |                          |                    |                    |
|--------------------------|--------------------------|--------------------|--------------------|
| Dielectric Strength      | Withstands 2000V minimum | Connection         | Back and side wire |
| Number of Wires          | 3                        | Temperature Rating | -40° - 60° C       |
| Amperage                 | 20 A                     | Number of Poles    | Double Pole        |
| Wire Size                | 14 - 10 AWG              | Voltage            | 125.0 V            |
| Environmental Conditions | Flammability: UL94 V2    |                    |                    |