



Heavy-Duty Decorator Spec Grade Single Receptacle Back and Side-Wire 20A 125V



## Features & Benefits

- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.
  - Heavy-duty compact design for easier installation and long lasting performance.
  - Impact-resistant nylon face.
  - Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire.
  - Tri-drive terminal and mounting screws.
  - For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
  - Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
  - Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact
- One-piece, brass, triple-wipe power contacts for lasting retention.
  - Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
  - Terminal compartments isolated from each other for positive conductor containment.
  - All devices fit standard #26 opening wall plate.
  - Auto-ground clip assures positive ground.
  - For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL498, cUL CSA		

---

## Dimensions

---

Product Width US	1.322 in	Product Depth US	1.188 in
Product Length US	2.635 in		

---

## Listing Agencies / 3rd Party Agencies

---

cUL ListingNumber	140596	cUL Listed	Yes
-------------------	--------	------------	-----

---

## Technical Information

---

Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
Number of Wires	3	Temperature Rating	-40° - 60° C
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Voltage	125.0 V
Environmental Conditions	Flammability: UL94 V2		

---