



Pass and Seymour 20A, 125V Turnlok® Ground Continuity Monitoring (GCM) Plug Part No. 26W47GCM

Rated watertight for 1,500 psi high-pressure hosedown, P&S watertight GCM plugs and connectors feature multiple seals to ensure protection against the environment. The transparent body houses dual LED lights with 360° visibility, indicating ground continuity and power status, while providing a NEMA 6P/IP67 rating.



Features & Benefits

Integral indication of ground continuity and power status. Convenient continuous monitoring enhances personnel safety.

Chemical- and impact-resistant nylon housing features horizontal, easy-grip ribs on back body.

Recessed cord-grip screw reduces screwdriver slippage for improved safety. Quick-thread tri-drive assembly and cord-grip screws come backed-out and ready-to-wire.

Color-coded terminal screws are positioned on the same plane and backed-out for fast installation.

For covering patents, see www.legrand.us/patents.

Dual, bright LED indicators with 360° degree visibility. Green LEDs indicate proper ground continuity and power status. Red LEDs indicate ground continuity loss or reversed polarity. No LED indicates open hot, open neutral, or hot to ground cross. For 250V configurations: Hot to ground cross will be indicated by a green and red LED.

Exclusive two-piece cord grip accepts a wide range of cord widths and provides more consistent pressure for superior conductor retention.

Internal dust shield keeps terminals free of contaminants.

Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.

Specifications

General Info

UPC Number	785007040654	Country Of Origin	United States
Product Line	Pass & Seymour	Standard	UL Listed, CSA Listed

Technical Information

Number of Poles	Double Pole	Voltage	125 V
Phase	Single	Wire Size	14 AWG min - 10 AWG max
Number of Wires	3	Environmental Conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed materials are UV stabilized