



Pass and Seymour

Discontinued - Heavy Duty Decorator Spec Grade Receptacles, Back and Side Wire, 20A 250V, Brown

Part No. 26852

Heavy-Duty Decorator Spec Grade Duplex Receptacle Back & Side Wire 20amp 250volt Brown

Features & Benefits

Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body. One-piece, brass, triple-wipe power contacts for lasting retention.

Heavy-duty compact design for easier installation and long lasting performance. Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Impact-resistant nylon face. Terminal compartments isolated from each other for positive conductor containment.

Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire. All devices fit standard #26 opening wall plate.

Tri-drive terminal and mounting screws. Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents. For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|------------|
| Product Line | Pass & Seymour | Color | Brown |
| Country Of Origin | Mexico | Application Sector | Commercial |
| Standard | UL498, cUL CSA | | |

Dimensions

| | | | |
|-------------------|----------|------------------|----------|
| Product Width US | 1.322 in | Product Depth US | 1.188 in |
| Product Length US | 2.635 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|---------------------|--------------------------|------------|--------------------|
| Dielectric Strength | Withstands 2000V minimum | Connection | Back and side wire |
|---------------------|--------------------------|------------|--------------------|

| | | | |
|-----------------|---|--------------------|--------------|
| Number of Wires | 3 | Temperature Rating | -40° - 60° C |
|-----------------|---|--------------------|--------------|

| | | | |
|----------|------|-----------------|-------------|
| Amperage | 20 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

| | | | |
|-----------|-------------|---------|---------|
| Wire Size | 14 - 10 AWG | Voltage | 250.0 V |
|-----------|-------------|---------|---------|

| | |
|--------------------------|-----------------------|
| Environmental Conditions | Flammability: UL94 V2 |
|--------------------------|-----------------------|
