



Pass and Seymour
Turnlok® SteriGuard™ Antimicrobial Plug, 20A 3Ø250V, 3-Pole/4-Wire, IP65 NEMA 4X/6P, NEMA L15-20P, Yellow
Part No. 26W75AM



SteriGuard Anti-Microbial Wiring Devices provide excellent protection against the growth of microbes on all surfaces. Independent testing proves the ability of these devices to inhibit the growth of Escherichia coli, Gram (-) and Staphylococcus aureus, Gram (+) providing long lasting benefits to manufacturers beyond conventional cleaning methods. Rated watertight for 1,500 psi high-pressure

Features & Benefits

UL and CSA Listed

NSF (National Sanitation Foundation) Certified

Patent Pending

Anti-microbial Additives Embedded in polymer and inhibits Growth of Bacteria, Molds, Mildews and Fungi

Anti-microbial Additive Resistant to Scuffing and Cleaning

Escherichia (E.Coli): - Log reduction greater than 4.8, reduced surface bacteria by greater than 99.99%

Staphylococcus (Staph), MRSA: - Log Reduction greater than 4.3, reduces surface bacteria by greater than 99.97%

Salmonella : Log Reduction Greater Than 3.6, reduces surface bacteria by Greater Than 99.97%

RoHS Compliant (Non-Halogenated)

Independently tested and Certified to JIS Z2801 standards

Resistant to High Pressure Hose-down applications

Tongue & Groove Environmental Sealing

Keyed Body and Cover for Alignment

NEMA Type 4, 4x, 6, 6P and IP67 Protection

SteriGuard: Anti-microbial Wiring Devices are ideal for a wide range of applications including food and beverage preparation, procession, & packaging: agriculture, pharmaceutical, and health care.

Specifications

General Info

| | | | |
|--------------|-----------------------|-------------------|---------------|
| Product Line | Pass & Seymour | Color | Yellow |
| UPC Number | 785007057270 | Country Of Origin | United States |
| Standard | UL Listed, CSA Listed | | |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 1.85 in | Product Depth US | 2.62 in |
| Product Height US | 1.85 in | | |

Technical Information

| | | | |
|-----------|-------------|--------------------------|--|
| Phase | Three | Number of Wires | 4 |
| Amperage | 20 A | Number of Poles | 3-Way |
| Wire Size | 14 - 10 AWG | Environmental Conditions | Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized |