



Pass and Seymour
Trademaster® 20A 125V Tamper-Resistant Duplex Receptacle, White
Part No. 3232TR20SW



Easily add the power every home needs with Legrand's 20A/125V Trademaster® Tamper-Resistant, Self-Grounding, Duplex Receptacle. This 20-amp receptacle offers a self-grounding feature that makes these receptacles ideal for residential and multi-dwelling units. Additionally, the receptacle has black "invisi-shutters" that are not visible by end users but help to prevent improper insertion of foreign objects to comply with NEC Article 406.12.

Features & Benefits

Ideal for Residential Applications & Multi-Dwelling units where 20A devices are required

Meets National Electric Code Tamper-Resistant requirements per Article 406.12

Black "Invisi-Shutters" disappear for an invisible effect

Side Wire Only accepts #12-#14 AWG

Auto-Ground Clip assures a positive ground connection is made

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Glossy	Country Of Origin	China
Receptacle Type	Straight Blade	Number of Receptacles	2
Construction	Injection molded plastic	Features	Self-Grounding
Outlet Type	Indoor, Self-Grounding, Tamper-Resistant	Package Quantity	1
Application Sector	Residential	Standard	RoHs, UL (UL498, E140596), cULus (UL498, E140596), CSA (C22.2 No. 42)
Warranty Type	1-Year Limited Warranty	Type	Decorator, Duplex, Outlet

Dimensions

Product Width US	1.42 in	Product Weight US	0.122 lb
------------------	---------	-------------------	----------

Product Depth US	1.03 in	Product Height US	4.2 in
------------------	---------	-------------------	--------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	UL498	cULus Listed	Yes
---------------------	-------	--------------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Is Tamper-Resistant	Yes	Connection	Side Wire Only
---------------------	-----	------------	----------------

Number of Wires	3	Amperage	20 A
-----------------	---	----------	------

Number of Poles	Double Pole	Wire Size	14 - 12 AWG
-----------------	-------------	-----------	-------------

Is Weather Resistant	No	Indoor/Outdoor	Indoor
----------------------	----	----------------	--------

NEMA Configuration Code	NEMA 5-20	Mounting Type	Box
-------------------------	-----------	---------------	-----

Voltage	125.0 V	Environmental Conditions	98% (relative humidity, non-condensing)
---------	---------	--------------------------	---
