



Heavy-Duty Spec Grade Single Receptacle Back and Side-Wire 15A 125V

Features & Benefits

Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Internal screw-pressure-plate back wire capable of accepting #14 - #10 AWG solid or stranded copper or copper-clad wire.

Tri-drive terminal and mounting screws.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.

Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

One-piece brass, triple-wipe power contacts for lasting retention.

Impact-resistant nylon face and thermoplastic back body.

Terminal compartments isolated from each other for positive conductor containment.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

| | | | |
|--------------------|----------------|-------------------|----------------------------------|
| Product Line | Pass & Seymour | Color | Black |
| UPC Number | 785007526127 | Country Of Origin | Mexico |
| Application Sector | Commercial | Standard | UL498, CSA C22.2 No. 42, FEDSPEC |

Dimensions

| | | | |
|-------------------|---------|------------------|----------|
| Product Width US | 1.32 in | Product Depth US | 1.093 in |
| Product Height US | 1.68 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|-------------------|--------|------------|-----|
| cUL ListingNumber | 140596 | cUL Listed | Yes |
|-------------------|--------|------------|-----|

Technical Information

| | | | |
|---------------------|--------------------------|--------------------------|-----------------------|
| Dielectric Strength | Withstands 2000V minimum | Connection | Back and side wire |
| Number of Wires | 3 | Temperature Rating | -40° - 60° C |
| Amperage | 15 A | Number of Poles | Double Pole |
| Wire Size | 14 - 10 AWG | Environmental Conditions | Flammability: UL94 V2 |