

This IBM® 46C3447 compatible SFP+ transceiver provides 10GBase-SR throughput up to 300m over multi-mode fiber (MMF) at a wavelength of 850nm using a LC connector. It is guaranteed to be 100% compatible with the equivalent IBM® transceiver. This easy to install, hot swappable transceiver has been programmed, uniquely serialized and data-traffic and application tested to ensure that it will initialize and perform identically. Digital optical monitoring (DOM) support is also present to allow access to real-time operating parameters. All Legrand transceivers are Trade Agreements Act (TAA) compliant.

Features & Benefits

LC ports designed for use with Multimode Fiber	Supports up to 300 meters of cabling
Supports Digital Optical Monitoring (DOM)	SFP+ transceiver module
850nm wavelength signaling	

Specifications

General Info

Product Line	Legrand	Color	Silver
UPC Number	757120669753	Country Of Origin	United States
Application Sector	Commercial/Industrial		

Buy American Act Compliance

TAA Compliant	Yes
---------------	-----

Additional Information

RoHS Conformant	Yes	Product Has Potential to Contribute to LEED	Yes
-----------------	-----	---	-----