




Wiremold
4IN PREWIRED FLUSH SYLE DUP CR SB
Part No. 4ATP2CRSB



Designed for retrofit and new construction, Evolution Series 4" Recessed Poke-Thru devices provide convenient access to power, communications, and audio/video services recessed below floor level - providing maximum device protection. With 2 Gangs of capacity, you will be able to configure services for the needs of your space. The low-profile metal covers are available in brushed aluminum, satin brass, satin nickel, and multiple powder-coated finishes designed to match any space. Evolution Series 4" Poke-Thru devices are the perfect fit for kiosks, training rooms, classrooms, healthcare facilities or commercial buildings with open-space architecture.

Features & Benefits

Prewired assembly: Save on labor with a completely assembled, prewired poke-thru with every power receptacle already installed.

Step-on-it installation: Quick and easy installation without the need for additional fasteners or a second installer.

Multiple finishes: Evolution Series Poke-Thru Devices are available in multiple finishes, (BK) black, (GY) gray, (BZ) bronze, (AL) aluminum, (AA) brushed aluminum, (SB) satin brass, and (SN) satin nickel to seamlessly match your environment.

2 hour fire rating: Evolution Series Poke-Thru Devices use an intumescent material that maintains the fire rating of any floor for up to 2 hours.

UL Listed and UL fire classified to U.S. and Canadian safety standards: UL Fire rated for up to 2-hour rated floors maintains the fire classification of the floor.

Recessed devices: All power devices are recessed below floor level, providing maximum protection and device longevity.

Unique cover design: The cover opens a full 180 degrees with two unique spring-loaded slide egress doors to keep wires, connections and people safe

Surface style cover assemblies: A surface style cover is for mounting on top of the finished floor surface. The surface cover is designed to be used for carpet, tile, wood, polished concrete, or terrazzo.

Wide trim flange is designed to meet the ADA Accessibility Guidelines as it pertains to ADA Standard 4.5 which addresses changes in floor and ground surface levels. The poke-thru trim flanges are beveled so the slope is no greater than 1:2 ratio.

Specifications

General Info

| | | | |
|-----------------|----------------|-----------------------|---------------|
| Product Line | Wiremold | Color | Brass |
| UPC Number | 786564105145 | Country Of Origin | United States |
| Receptacle Type | Straight Blade | Number of Receptacles | 1 |

| | | | |
|---------------------------------------------|--------------------------------|-------------------------|------------------------------------------------------|
| Features | Recessed | Cover Style | Flush |
| Number of Knockouts | 10 | Application Sector | Commercial, Education, Healthcare, Hospitality |
| Standard | UL Fire Classified, cULus, NEC | Warranty Type | 1-Year from Installation or 2-Years from Day of Sale |
| Type | Poke-Thru | | |
| Dimensions | | | |
| Product Width US | 5.5 in | Product Weight US | 6.1 lb |
| Product Height US | 18.563 in | Product Length US | 5.5 in |
| Cubic Capacity | 25 in ³ | Core Hole Size | 4 in |
| Knockout Size | 1-1/2 in, 3/4 in | | |
| Listing Agencies / 3rd Party Agencies | | | |
| cULus Listed | Yes | | |
| Additional Information | | | |
| Product Has Potential to Contribute to LEED | Yes | | |
| Technical Information | | | |
| Floor Type | Carpet, Concrete, Tile, Wood | Is Tamper-Resistant | No |
| Is Pre-Wired | Yes | Service Capacity | Dual |
| Fire Rating | 2 hr | Amperage | 20 A |
| Current Rating | 20 A | NEMA Configuration Code | 5-20R |
| Number of Outlets | 2 | Voltage | 125.0 V |