



Industrial Extra Heavy-Duty Spec Grade Duplex Receptacle Back and Side-Wire 15A 125V

Features & Benefits

| | |
|---|--|
| One-piece brass mounting strap with integral ground. | Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body. |
| Two drive screws anchor strap to back body and face. | Exclusive patented feature, circuit label on face allows permanent circuit identification. |
| .036 inch thick, brass, triple-wipe power contacts for lasting retention. | Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. |
| Impact-resistant nylon face and back body. | Oversized #10 deep tri-drive head brass terminal and ground screws. |
| Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation. | External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection. |
| Line terminals accept #14 -- #10 AWG stranded or solid copper clad conductors. | Auto-ground clip assures positive ground. |
| Corrosion-resistant models have nickel-plated straps and contacts. | For covering patents, see www.legrand.us/patents . |
| For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here . | Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact |

Specifications

General Info

| | | | |
|--------------|----------------|-------------------|--------|
| Product Line | Pass & Seymour | Color | Red |
| UPC Number | 785007528077 | Country Of Origin | Mexico |

| | | | |
|--------------------|-------------------------|----------|-----------------------|
| Application Sector | Commercial, Residential | Standard | UL 498, 1449, FEDSPEC |
|--------------------|-------------------------|----------|-----------------------|

Dimensions

| | | | |
|-------------------|----------|------------------|---------|
| Product Width US | 1.625 in | Product Depth US | 0.86 in |
| Product Height US | 2.75 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|-----------|-------------|-----------------|-------------|
| Phase | Three | Number of Wires | 3 |
| Amperage | 15 A | Number of Poles | Double Pole |
| Wire Size | 14 - 10 AWG | | |