



Industrial Extra Heavy-Duty Spec Grade Duplex Receptacle Back and Side-Wire 15A 125V

## Features & Benefits

- One-piece brass mounting strap with integral ground.      Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
- Two drive screws anchor strap to back body and face.      Exclusive patented feature, circuit label on face allows permanent circuit identification.
- .036 inch thick, brass, triple-wipe power contacts for lasting retention.      Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and back body.      Oversized #10 deep tri-drive head brass terminal and ground screws.
- Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.      External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.
- Line terminals accept #14 -- #10 AWG stranded or solid copper clad conductors.      Auto-ground clip assures positive ground.
- Corrosion-resistant models have nickel-plated straps and contacts.      For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).      Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.  
 Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Red
Country Of Origin	Mexico	Application Sector	Residential/Commercial

---

Standard

UL 498, 1449

---

## Dimensions

---

Product Width US

1.625 in

Product Depth US

0.86 in

---

Product Height US

2.75 in

---

## Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber

140596

cULus Listed

Yes

---

## Technical Information

---

Phase

3

Number of Wires

3

---

Amperage

15 A

Number of Poles

Double Pole

---

Wire Size

14 - 10 AWG

Voltage

125.0 V

---