



Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (LED Indicator only). Back & Side Wire, 15amp 125volt, Light Almond.

Features & Benefits

Solid-state LED monitor has 25-year minimum life expectancy. A high visibility, wide-angle lens indicates protection is in place.

Wrap-around steel strap for structural integrity. Auto-ground is standard, for easier installation.

Triple-wipe, copper-alloy contacts for superior, more dependable connection.

Thermal protection in 3 modes. Three 17mm dual pack MOVs absorb up to 340 Joules per leg (L-N, L-G, N-G) with 24,000 amp current handling for full, equal, and symmetrical protection. Response time is less than one nanosecond.

LED Indication: Steady green = protected, Flashing re = not protected, OFF = no power to unit

Impact-resistant thermoplastic exterior resists impacts and scrapes.

External screw-pressure-plate back and side wire terminals, including ground, with exclusive back wire clamps accept #14-#10 AWG copper or copper-clad, solid or stranded conductors. Pressure plate allows two conductors to be terminated by a single screw.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	5262LASP
UPC Number	785007193947	Country Of Origin	Mexico

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Amperage

15 A
