

Heavy-Duty Spec Grade Single Receptacle Back and Side-Wire 15A 125V



## Features & Benefits

Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Internal screw-pressure-plate back wire capable of accepting #14 - #10 AWG solid or stranded copper or copper-clad wire.

Tri-drive terminal and mounting screws.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.

Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

One-piece brass, triple-wipe power contacts for lasting retention.

Impact-resistant nylon face and thermoplastic back body.

Terminal compartments isolated from each other for positive conductor containment.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

## Specifications

### General Info

|                    |                |                   |                                  |
|--------------------|----------------|-------------------|----------------------------------|
| Product Line       | Pass & Seymour | Color             | White                            |
| UPC Number         | 785007526158   | Country Of Origin | Mexico                           |
| Application Sector | Commercial     | Standard          | UL498, CSA C22.2 No. 42, FEDSPEC |

Dimensions

|                   |         |                  |          |
|-------------------|---------|------------------|----------|
| Product Width US  | 1.32 in | Product Depth US | 1.093 in |
| Product Height US | 1.68 in |                  |          |

Listing Agencies / 3rd Party Agencies

|                   |        |            |     |
|-------------------|--------|------------|-----|
| cUL ListingNumber | 140596 | cUL Listed | Yes |
|-------------------|--------|------------|-----|

Technical Information

|                     |                          |                          |                       |
|---------------------|--------------------------|--------------------------|-----------------------|
| Dielectric Strength | Withstands 2000V minimum | Connection               | Back and side wire    |
| Number of Wires     | 3                        | Temperature Rating       | -40° - 60° C          |
| Amperage            | 15 A                     | Number of Poles          | Double Pole           |
| Wire Size           | 14 - 10 AWG              | Environmental Conditions | Flammability: UL94 V2 |