



Surge Protective Extra Heavy-Duty Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). Back & Side Wire, 15amp 125volt, Gray.

Features & Benefits

Solid-state LED monitor has 25-year minimum life expectancy. A high visibility, wide-angle lens indicates protection is in place.	Corrosion-resistant, plated and tabbed steel strap locked in to face and back body to resist pulling away from face/body assembly.
Audible alarm alert of MOV damage. Alarm able to be turned On/Off.	Wrap-around steel strap for structural integrity. Auto-ground is standard, for easier installation.
Impact-resistant thermoplastic exterior resists impacts and scrapes.	Triple-wipe, copper-alloy contacts for superior, more dependable connection.
Thermal protection in 3 modes. 3 17mm dual pack MOVs absorb up to 340 Joules of excess energy in each leg (L-N, L-G, N-G) with 24,000 amp current handling capability for full, equal and symmetrical protection. Protection response time in less than one nanosecond.	For covering patents, see www.legrand.us/patents .

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	PT5262GRYSP
Color	Gray	Country Of Origin	Mexico

Dimensions

Product Width US	1.7 in	Product Depth US	0.875 in
Product Height US	2.75 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Amperage	15 A
----------	------
