



Hard Use Spec Grade Duplex Receptacle Back and Side Wire 15A 125V



Features & Benefits

- Corrosion-resistant, plated and tabbed steel strap locked in to face and back body to resist pulling away from face/body assembly.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

8 hole internal screw-pressure-plate back wire terminals accept #10 - #14 AWG solid or stranded copper or copper-clad conductors.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).
- LED Indication: Steady green = protected, Flashing re = not protected, OFF = no power to unit

Impact-resistant nylon face.

Terminal compartments isolated from each other for positive conductor containment.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.

Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

|                       |                         |                   |                         |
|-----------------------|-------------------------|-------------------|-------------------------|
| Product Line          | Pass & Seymour          | Color             | White                   |
| Finish                | Matte                   | Country Of Origin | Mexico                  |
| Number of Receptacles | 2                       | Outlet Type       | Commercial, Indoor      |
| Application Sector    | Commercial              | Standard          | UL498, CSA C22.2 No. 42 |
| Warranty Type         | 1-Year Limited Warranty | Type              | Outlet                  |



Dimensions

|                   |          |                  |         |
|-------------------|----------|------------------|---------|
| Product Width US  | 1.322 in | Product Depth US | 0.78 in |
| Product Height US | 2.635 in |                  |         |

Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

|                     |                          |                    |              |
|---------------------|--------------------------|--------------------|--------------|
| Dielectric Strength | Withstands 2000V minimum | Temperature Rating | -40° - 60° C |
| Amperage            | 15 A                     | Number of Poles    | Double Pole  |
| Wire Size           | 14 - 10 AWG              | Indoor/Outdoor     | Indoor       |
| Voltage             | 125.0 V                  |                    |              |