



Heavy-Duty Spec Grade Single Receptacle Side Wire 20A 125V

## Features & Benefits

Auto-ground clip assures positive ground.

Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.

One-piece brass triple-wire power contacts for lasting retention.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Factory-broken split-circuit tab allows for 50% plug load control to be achieved in one duplex receptacle.

Backed-out tri-drive steel terminal screws. Internal screw-pressure-plate side wire capability.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

|                    |                         |                       |              |
|--------------------|-------------------------|-----------------------|--------------|
| Product Line       | Pass & Seymour          | Color                 | White        |
| Finish             | Matte                   | UPC Number            | 785007535150 |
| Country Of Origin  | Mexico                  | Number of Receptacles | 1            |
| Application Sector | Commercial              | Standard              | UL 498       |
| Warranty Type      | 1-Year Limited Warranty | Type                  | Outlet       |

### Dimensions

|                  |         |                  |         |
|------------------|---------|------------------|---------|
| Product Width US | 1.38 in | Product Depth US | 1.08 in |
|------------------|---------|------------------|---------|

Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

|          |      |                 |             |
|----------|------|-----------------|-------------|
| Amperage | 20 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

|           |       |                |        |
|-----------|-------|----------------|--------|
| Wire Size | 4 AWG | Indoor/Outdoor | Indoor |
|-----------|-------|----------------|--------|