



Pass and Seymour  
20A 125V Extra Heavy Duty Spec-Grade Surge Protective Duplex Receptacle, Black  
Part No. 5362BKSP



Surge Protective Extra Heavy-Duty Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). Specification grade surge suppressor receptacle with audible alarm and LED indicator, ideal for heavy duty power applications. By Pass and Seymour. Back and Side Wire, 20A, 125V.

Features & Benefits

|   |   |
|---|---|
| Solid-state LED monitor has 25-year minimum life expectancy. A high visibility, wide-angle lens indicates protection is in place.   | .032 inch thick, brass, triple-wipe power contacts for lasting retention.                           |
| Audible alarm alert of MOV damage. Alarm able to be turned On/Off.  | Wrap-around steel strap for structural integrity. Auto-ground is standard, for easier installation. |
| Impact-resistant thermoplastic exterior resists impacts and scrapes.  | Triple-wipe, copper-alloy contacts for superior, more dependable connection.                        |
| Thermal protection in 3 modes. 3 17mm dual pack MOVs absorb up to 340 Joules of excess energy in each leg (L-N, L-G, N-G) with 24,000 amp current handling capability for full, equal and symmetrical protection. Protection response time in less than one nanosecond. | For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .      |

Specifications

General Info

|                    |                        |                   |                   |
|--------------------|------------------------|-------------------|-------------------|
| Product Line       | Pass & Seymour         | Country Of Origin | China             |
| Application Sector | Residential/Commercial | Standard          | RoHS, cULus, FSUL |

Dimensions

|                   |         |                  |          |
|-------------------|---------|------------------|----------|
| Product Width US  | 1.75 in | Product Depth US | 1.225 in |
| Product Height US | 2.8 in  |                  |          |

Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

|            |                  |                          |                    |
|------------|------------------|--------------------------|--------------------|
| Phase      | Single           | Frequency Rating         | 60 Hz              |
| Connection | Side & Back Wire | Class                    | IG                 |
| Amperage   | 20 A             | Type of Indicators       | LED, Audible Alarm |
| Voltage    | 125.0 V          | Environmental Conditions | UL94 V2            |