



Pass and Seymour
20A 125V Half-Controlled Plug Load Duplex Receptacle, Gray
Part No. 5362CHGRY



Permanent controlled receptacle marking allows for long-lasting, easy identification of controlled receptacle for end-users. NEMA-approved and compliant with 2014 NEC, CA Title 24, and ASHRAE Energy Efficiency Standard 90.1.

Features & Benefits

- Can be wired to any number of system-based or stand-alone plug load control solutions. Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- Corrosion-resistant, plated and tabbed steel strap locked in to face and back body to resist pulling away from face/body assembly. .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Impact-resistant nylon face.
- Terminal compartments isolated from each other for positive conductor containment. Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.

Specifications

General Info

| | | | |
|-----------------------|-------------------------|-------------------|----------------------|
| Product Line | Pass & Seymour | Color | Gray |
| UPC Number | 785007038293 | Country Of Origin | Mexico |
| Number of Receptacles | 2 | Outlet Type | Energy Saving On/Off |
| Application Sector | Commercial | Standard | FEDSPEC |
| Warranty Type | 1-Year Limited Warranty | Type | Outlet |

Dimensions

| | | | |
|------------------|---------|------------------|---------|
| Product Width US | 1.32 in | Product Depth US | 0.78 in |
|------------------|---------|------------------|---------|

| | |
|-------------------|----------|
| Product Height US | 2.635 in |
|-------------------|----------|

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|---------|--------------|-----|
| cULus ListingNumber | E140596 | cULus Listed | Yes |
|---------------------|---------|--------------|-----|

Technical Information

| | | | |
|----------|------|-----------------|-------------|
| Amperage | 20 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

| | |
|----------------|--------|
| Indoor/Outdoor | Indoor |
|----------------|--------|
