



Heavy-Duty Spec Grade Single Receptacle Side Wire 15A 250V

Features & Benefits

Auto-ground clip assures positive ground.

Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.

One-piece brass triple-wire power contacts for lasting retention.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.

Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

One-piece heat-treated triple-wipe brass power contacts.

Backed-out tri-drive steel terminal screws.
Internal screw-pressure-plate back and side wire capability. Two back wire holes for increased wiring flexibility.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007565157
Country Of Origin	Mexico	Number of Receptacles	1
Application Sector	Commercial	Standard	UL498, CSA C22.2 No. 42
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.38 in	Product Depth US	1.08 in
------------------	---------	------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
Number of Wires	3	Temperature Rating	-40° - 60° C
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
Environmental Conditions	Flammability: UL94 V2		