



Industrial Extra Heavy-Duty Spec Grade Duplex Receptacle Back and Side-Wire 15A 250V

Features & Benefits

- One-piece brass mounting strap with integral ground. Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
- Two drive screws anchor strap to back body and Exclusive patented feature, circuit label on face allows permanent circuit face identification.
- .036 inch thick, brass, triple-wipe power contacts for lasting retention. Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and back body. Oversized #10 deep tri-drive head brass terminal and ground screws.
- Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation. External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.
- Line terminals accept #14 -- #10 AWG stranded or solid copper clad conductors. Auto-ground clip assures positive ground.
- Corrosion-resistant models have nickel-plated straps and contacts. For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here. Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	Mexico	Application Sector	Residential/Commercial

Standard

UL 498, WC596

Dimensions

Product Width US

1.625 in

Product Depth US

0.9 in

Product Height US

2.75 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber

140596

cULus Listed

Yes

Technical Information

Phase

3

Number of Wires

3

Amperage

15 A

Number of Poles

Double Pole

Wire Size

14 - 10 AWG

Voltage

250.0 V
