



Quiktron
Q-Series Patch Cords, CAT6, Non-Booted, Red, 25 FT
Part No. 566-130-025



Q-Series patch cords are a perfect solution for when cost and speed of delivery are top priority. Designed to perform to TIA-568.2-D standards, Q-Series cords are available in a full range of colors and lengths, stocked and ready to order.

Features & Benefits

Connector: 50micron gold plated RJ45 male to male

Conductor: 24AWG stranded copper

Warranty Type: Lifetime warranty

Price Sensitive: Perfect solution for when cost and speed of delivery are top priority

Standards Compliant: Perform to TIA-568.2-D standards

Specifications

General Info

| | | | |
|---------------|-------------------|--------------------|------------------------|
| Product Line | Quiktron | Color | Red |
| UPC Number | 884815751643 | Country Of Origin | Vietnam |
| Features | Standard Diameter | Application Sector | Commercial, Industrial |
| Warranty Type | 5-Year | Type | Copper Patch Cord |

Dimensions

| | | | |
|-------------------|----------|-------------------|---------|
| Product Weight US | 0.625 lb | Product Length US | 25.0 FT |
| Cable Length | 25 ft | | |

Additional Information

| | |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

Technical Information

| | | | |
|-----------------------------|---------------------------|---------------------------|---------------------------|
| Jacket Material | PVC | Operating Temperature Min | -10 °C |
| Category Performance Rating | Cat6 | Compatibility | RJ-45 |
| Wire Gauge | 24 AWG | Storage Humidity | 0-90% RH (Non-Condensing) |
| Plating Specification | 50 µ in Gold | Jacket Application | Riser Rated |
| Bend Radius | 0.896 in | Shielded/Unshielded | Unshielded |
| Termination Style | Pre-Terminated | Conductor Stranding | Stranded |
| Operating Temperature Max | 60 °C | Cable Type | Non-Booted |
| Jacket Rating | CM Rated | Cable Diameter | 0.224 in |
| Braid | Non-braided Wiring | Connector 2 | RJ-45 Male |
| Connector 1 | RJ-45 Male | Operating Temperature | -10°-60°C |
| Operating Humidity | 0-90% RH (Non-Condensing) | Conductor Material | Copper |
| Voltage | 300.0 V | Storage Temperature | -40° - 60° C |