



Heavy-Duty Hospital Grade Compact Design Duplex Receptacle Back and Side Wire 15A 125V

Features & Benefits

| | |
|---|---|
| Impact-resistant nylon face. | One-piece heat-treated triple-wipe brass power contacts. |
| Easily accessible break-off line contact connecting tab for split circuit wiring. | Corrosion-resistant, zinc-plated steel strap is locked in. |
| Internal screw-pressure-plate back wire and side wire line terminals accept #14 : #10 AWG copper or copper-clad conductors. | High strength thermoplastic back body. |
| Auto-ground clip assures positive ground. | Compact design for easy installation. |
| Tri-drive terminal and mounting screws. | Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact |

Specifications

General Info

| | | | |
|--------------------|----------------------------|-----------------------|----------------------------------|
| Product Line | Pass & Seymour | Color | White |
| Finish | Matte | UPC Number | 785007820058 |
| Country Of Origin | Mexico | Number of Receptacles | 2 |
| Application Sector | Commercial, Hospital Grade | Standard | UL498, CSA C22.2 No. 42, FEDSPEC |
| Warranty Type | 1-Year Limited Warranty | Type | Outlet |

Dimensions

| | | | |
|------------------|----------|------------------|---------|
| Product Width US | 1.322 in | Product Depth US | 0.78 in |
|------------------|----------|------------------|---------|

| | |
|-------------------|----------|
| Product Height US | 3.281 in |
|-------------------|----------|

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|---------------------|--------------------------|--------------------|--------------|
| Dielectric Strength | Withstands 2000V minimum | Temperature Rating | -40° - 60° C |
|---------------------|--------------------------|--------------------|--------------|

| | | | |
|----------|------|-----------------|-------------|
| Amperage | 15 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

| | | | |
|-----------|-------------|----------------|--------|
| Wire Size | 14 - 10 AWG | Indoor/Outdoor | Indoor |
|-----------|-------------|----------------|--------|