



Heavy-Duty Hospital Grade Compact Design Duplex Receptacle Back and Side Wire 15A 125V



Features & Benefits

Impact-resistant nylon face.

One-piece heat-treated triple-wipe brass power contacts.

Easily accessible break-off line contact connecting tab for split circuit wiring.

Corrosion-resistant, zinc-plated steel strap is locked in.

Internal screw-pressure-plate back wire and side wire line terminals accept #14 : #10 AWG High strength thermoplastic back body. copper or copper-clad conductors.

Auto-ground clip assures positive ground.

Compact design for easy installation.

Tri-drive terminal and mounting screws.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Commercial, Indoor	Application Sector	Commercial
Standard	UL498, CSA C22.2 No. 42	Warranty Type	1-Year Limited Warranty
Type	Outlet		

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
------------------	----------	------------------	---------

Product Height US 3.281 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber 140596 cULus Listed Yes

Technical Information

Dielectric Strength Withstands 2000V minimum Connection Back and side wire

Number of Wires 3 Temperature Rating -40° - 60° C

Amperage 15 A Number of Poles Double Pole

Wire Size 14 - 10 AWG Indoor/Outdoor Indoor

Voltage 125.0 V Environmental Conditions Flammability: UL94 V2
