



Heavy-Duty Hospital Grade Compact Design Duplex Receptacle Back and Side Wire 15A 125V



Features & Benefits

Impact-resistant nylon face.

One-piece heat-treated triple-wipe brass power contacts.

Easily accessible break-off line contact connecting tab for split circuit wiring.

Corrosion-resistant, zinc-plated steel strap is locked in.

Internal screw-pressure-plate back wire and side wire line terminals accept #14 : #10 AWG copper or copper-clad conductors.

High strength thermoplastic back body.

Auto-ground clip assures positive ground.

Compact design for easy installation.

Tri-drive terminal and mounting screws.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

| | | | |
|-----------------------|-------------------------|-------------------|-------------------------|
| Product Line | Pass & Seymour | Color | Ivory |
| Finish | Matte | Country Of Origin | Mexico |
| Number of Receptacles | 2 | Outlet Type | Commercial, Indoor |
| Application Sector | Commercial | Standard | UL498, CSA C22.2 No. 42 |
| Warranty Type | 1-Year Limited Warranty | Type | Outlet |

Dimensions

| | | | |
|------------------|----------|------------------|---------|
| Product Width US | 1.322 in | Product Depth US | 0.78 in |
|------------------|----------|------------------|---------|

| | |
|-------------------|----------|
| Product Height US | 3.281 in |
|-------------------|----------|

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|---------------------|--------------------------|--------------------|--------------|
| Dielectric Strength | Withstands 2000V minimum | Temperature Rating | -40° - 60° C |
|---------------------|--------------------------|--------------------|--------------|

| | | | |
|----------|------|-----------------|-------------|
| Amperage | 15 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

| | | | |
|-----------|-------------|----------------|--------|
| Wire Size | 14 - 10 AWG | Indoor/Outdoor | Indoor |
|-----------|-------------|----------------|--------|

| | |
|---------|---------|
| Voltage | 125.0 V |
|---------|---------|
