



Extra Heavy-Duty Hospital Grade Duplex Receptacle Back and Side Wire 15A 125V

## Features & Benefits

One-piece nickel-plated brass mounting strap with integral ground.

Two drive screws anchor strap to back body and face.

.040 inch thick, nickel-plated brass, triple-wipe power contacts for lasting retention.

Oversized #10 deep tri-drive head brass terminal and ground screws.

External nickel-plated screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.  
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.

Exclusive patented feature, circuit label on face allows permanent circuit identification.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007820119
Country Of Origin	Mexico	Number of Receptacles	2

Features	Brass Mounting Strap	Outlet Type	Hospital Grade
Application Sector	Commercial, Healthcare	Wall Plate Included	No
Standard	cULus UL498, CSA C22.2 No. 42	Warranty Type	1-Year Limited Warranty
<b>Dimensions</b>			
Product Width US	1.625 in	Product Depth US	0.866 in
Product Height US	2.75 in		
<b>Listing Agencies / 3rd Party Agencies</b>			
cULus ListingNumber	E140596	cULus Listed	Yes
<b>Technical Information</b>			
Operating Temperature Min	-40 °C	Dielectric Strength	Withstands 2000V minimum
Connection Location	Back and Side	Number of Wires	3
Operating Temperature Max	60 °C	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-15R
Operating Temperature	-40°-60°C	Wire Connection Type	Screw Terminals
Voltage	125.0 V		