



Pass and Seymour
15A 125V Extra Heavy Duty Hospital-Grade Duplex Receptacle, Back and Side Wire, Red
Part No. 8200RED



Extra Heavy-Duty Hospital Grade Duplex Receptacle Back and Side Wire 15A 125V

Features & Benefits

One-piece nickel-plated brass mounting strap with integral ground.

Two drive screws anchor strap to back body and face.

.040 inch thick, nickel-plated brass, triple-wipe power contacts for lasting retention.

Oversized #10 deep tri-drive head brass terminal and ground screws.

External nickel-plated screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.

Exclusive patented feature, circuit label on face allows permanent circuit identification.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
UPC Number	785007820102	Country Of Origin	Mexico
Number of Receptacles	2	Application Sector	Commercial, Hospital Grade

Standard	cULus UL498, CSA C22.2 No. 42, FDSPEC	Type	Outlet
Dimensions			
Product Width US	1.625 in	Product Depth US	0.866 in
Product Height US	2.75 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	140596	cULus Listed	Yes
Technical Information			
Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
Number of Wires	3	Temperature Rating	-40° - 60° C
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
Environmental Conditions	Flammability: UL94 V2 and UL94-5 VA		