



Pass and Seymour
20A 125V Hospital-Grade Surge Protective Duplex Receptacle, Gray
Part No. 8300GRYSP



Hospital Grade Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). Back and Side Wire, 20A, 125V, Blue.

Features & Benefits

Solid-state LED monitor has 25-year minimum life expectancy. A high visibility, wide-angle lens indicates protection is in place.

Audible alarm alert of MOV damage. Alarm able to be turned On/Off.

Impact-resistant thermoplastic exterior resists impacts and scrapes.

Thermal protection in 3 modes. 3 17mm dual pack MOVs absorb up to 340 Joules of excess energy in each leg (L-N, L-G, N-G) with 24,000 amp current handling capability for full, equal and symmetrical protection.

For covering patents, see www.legrand.us/patents.

One-piece brass, triple-wipe power contacts for lasting retention.

Wrap-around steel strap for structural integrity. Auto-ground is standard, for easier installation.

Triple-wipe, copper-alloy contacts for superior, more dependable connection.

Protection response time in less than one nanosecond.

Specifications

General Info

| | | | |
|--------------------|----------------|-------------------|---|
| Product Line | Pass & Seymour | Color | Gray |
| UPC Number | 785007193565 | Country Of Origin | Mexico |
| Application Sector | Commercial | Standard | cUL UL1449, UL498: CSA C22.2 No. 42: ANSI/IEEE C62.41 (Formerly IEEE 587), ANSI/IEEE C62.45 Installation Categories "A" (Ring Wave) "B" (Unidirectional Impulse). |

Dimensions

| | | | |
|---------------------------------------|--------------------|--------------------------|-----------------------|
| Product Width US | 1.75 in | Product Depth US | 1.225 in |
| Product Height US | 2.8 in | | |
| Listing Agencies / 3rd Party Agencies | | | |
| cULus ListingNumber | 140596 | cULus Listed | Yes |
| Technical Information | | | |
| Connection | Back and side wire | Class | IG |
| Amperage | 20 A | Environmental Conditions | Flammability: UL94 V2 |