

Heavy-Duty Hospital Grade Compact Design Duplex Receptacle Back and Side Wire 20A 125V



Features & Benefits

Impact-resistant nylon face.	.032 inch thick, brass, triple-wipe power contacts for lasting retention.
Easily accessible break-off line contact connecting tab for split circuit wiring.	Corrosion-resistant, zinc-plated steel strap is locked in.
Internal screw-pressure-plate back wire and side wire line terminals accept #14 : #10 AWG copper or copper-clad conductors.	High strength thermoplastic back body.
Auto-ground clip assures positive ground.	Compact design for easy installation.
Tri-drive terminal and mounting screws.	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Commercial, Indoor
Application Sector	Commercial	Standard	UL498, CSA C22.2 No. 42
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	3.281 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	140596	cULus Listed	Yes
Technical Information			
Dielectric Strength	Withstands 2000V minimum	Temperature Rating	-40° - 60° C
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
Voltage	125.0 V		