



Pass and Seymour
20A 125V Hospital-Grade Surge Protective Duplex Receptacle, Light Almond
Part No. 8300LASP



Hospital Grade Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). Back and Side Wire, 20A, 125V, Blue.

Features & Benefits

Solid-state LED monitor has 25-year minimum life expectancy. A high visibility, wide-angle lens indicates protection is in place.	One-piece brass, triple-wipe power contacts for lasting retention.
Audible alarm alert of MOV damage. Alarm able to be turned On/Off.	Wrap-around steel strap for structural integrity. Auto-ground is standard, for easier installation.
Impact-resistant thermoplastic exterior resists impacts and scrapes.	Triple-wipe, copper-alloy contacts for superior, more dependable connection.
Thermal protection in 3 modes. 3 17mm dual pack MOVs absorb up to 340 Joules of excess energy in each leg (L-N, L-G, N-G) with 24,000 amp current handling capability for full, equal and symmetrical protection.	Protection response time in less than one nanosecond.
For covering patents, see www.legrand.us/patents .	

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007194043
Country Of Origin	Mexico	Application Sector	Commercial
Standard	cUL UL1449, UL498: CSA C22.2 No. 42: ANSI/IEEE C62.41 (Formerly IEEE 587), ANSI/IEEE C62.45 Installation Categories "A" (Ring Wave) "B" (Unidirectional Impulse).		

Dimensions

Product Width US	1.75 in	Product Depth US	1.225 in
------------------	---------	------------------	----------

Product Height US	2.8 in
-------------------	--------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Connection	Back and side wire	Class	IG
------------	--------------------	-------	----

Amperage	20 A	Environmental Conditions	Flammability: UL94 V2
----------	------	--------------------------	--------------------------