



Hospital Grade Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). Back and Side Wire, 20A, 125V, Blue.

## Features & Benefits

|  |  |
|--|--|
| <p>Solid-state LED monitor has 25-year minimum life expectancy. A high visibility, wide-angle lens indicates protection is in place.</p>   | <p>One-piece brass, triple-wipe power contacts for lasting retention.</p>                                  |
| <p>Audible alarm alert of MOV damage. Alarm able to be turned On/Off.</p>  | <p>Wrap-around steel strap for structural integrity. Auto-ground is standard, for easier installation.</p> |
| <p>Impact-resistant thermoplastic exterior resists impacts and scrapes.</p>  | <p>Triple-wipe, copper-alloy contacts for superior, more dependable connection.</p>                        |
| <p>Thermal protection in 3 modes. 3 17mm dual pack MOVs absorb up to 340 Joules of excess energy in each leg (L-N, L-G, N-G) with 24,000 amp current handling capability for full, equal and symmetrical protection. Protection response time in less than one nanosecond.</p> | <p>For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a>.</p>       |

## Specifications

### General Info

|                   |  |                    |            |
|-------------------|--|--------------------|------------|
| Product Line      | Pass & Seymour   | Color              | White      |
| Country Of Origin | Mexico   | Application Sector | Commercial |
| Standard          | cUL UL1449, UL498: CSA C22.2 No. 42:<br>ANSI/IEEE C62.41 (Formerly IEEE 587),<br>ANSI/IEEE C62.45 Installation Categories "A"<br>(Ring Wave) "B" (Unidirectional Impulse). |                    |            |

### Dimensions

|                  |         |                  |          |
|------------------|---------|------------------|----------|
| Product Width US | 1.75 in | Product Depth US | 1.225 in |
|------------------|---------|------------------|----------|

---

Product Height US      2.8 in

---

**Listing Agencies / 3rd Party Agencies**

---

cULus ListingNumber      140596      cULus Listed      Yes

---

**Technical Information**

---

Connection      Back and side wire      Class      IG

---

Amperage      20 A      Voltage      125.0 V

---

Environmental Conditions      Flammability: UL94 V2

---