



Hospital Grade Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). Back and Side Wire, 20A, 125V, Blue.

Features & Benefits

<p>Solid-state LED monitor has 25-year minimum life expectancy. A high visibility, wide-angle lens indicates protection is in place.</p>	<p>One-piece brass, triple-wipe power contacts for lasting retention.</p>
<p>Audible alarm alert of MOV damage. Alarm able to be turned On/Off.</p>	<p>Wrap-around steel strap for structural integrity. Auto-ground is standard, for easier installation.</p>
<p>Impact-resistant thermoplastic exterior resists impacts and scrapes.</p>	<p>Triple-wipe, copper-alloy contacts for superior, more dependable connection.</p>
<p>Thermal protection in 3 modes. 3 17mm dual pack MOVs absorb up to 340 Joules of excess energy in each leg (L-N, L-G, N-G) with 24,000 amp current handling capability for full, equal and symmetrical protection. Protection response time in less than one nanosecond.</p>	<p>For covering patents, see www.legrand.us/patents.</p>

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
Country Of Origin	Mexico	Application Sector	Commercial
Standard	cUL UL1449, UL498: CSA C22.2 No. 42: ANSI/IEEE C62.41 (Formerly IEEE 587), ANSI/IEEE C62.45 Installation Categories "A" (Ring Wave) "B" (Unidirectional Impulse).		

Dimensions

Product Width US	1.75 in	Product Depth US	1.225 in
------------------	---------	------------------	----------

Product Height US 2.8 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber 140596 cULus Listed Yes

Technical Information

Connection Back and side wire Class IG

Amperage 20 A Voltage 125.0 V

Environmental Conditions Flammability: UL94 V2
