



Heavy-Duty Hospital Grade Single Receptacle Back and Side Wire 20A 125V

Features & Benefits

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly. .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Impact-resistant nylon face and thermoplastic back body.
- Internal screw-pressure-plate back wire capable of accepting #14 : #10 AWG solid or stranded copper or copper-clad wire. Terminal compartments isolated from each other for positive conductor containment.
- Auto-ground clip assures positive ground. For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here. Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

| | | | |
|-------------------|-----------------------------|-----------------------|------------|
| Product Line | Pass & Seymour | Color | Gray |
| Country Of Origin | Mexico | Number of Receptacles | 1 |
| Outlet Type | Commercial, Indoor | Application Sector | Commercial |
| Standard | UL498, cUL/CSA C22.2 No. 42 | Type | Outlet |

Dimensions

| | | | |
|------------------|---------|------------------|----------|
| Product Width US | 1.32 in | Product Depth US | 1.093 in |
|------------------|---------|------------------|----------|

| | |
|-------------------|---------|
| Product Height US | 3.68 in |
|-------------------|---------|

Listing Agencies / 3rd Party Agencies

| | | | |
|-------------------|--------|------------|-----|
| cUL ListingNumber | 140596 | cUL Listed | Yes |
|-------------------|--------|------------|-----|

Technical Information

| | | | |
|---------------------|--------------------------|------------|--------------------|
| Dielectric Strength | Withstands 2000V minimum | Connection | Back and side wire |
|---------------------|--------------------------|------------|--------------------|

| | | | |
|-----------------|---|--------------------|--------------|
| Number of Wires | 3 | Temperature Rating | -40° - 60° C |
|-----------------|---|--------------------|--------------|

| | | | |
|----------|------|-----------------|-------------|
| Amperage | 20 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

| | | | |
|-----------|-------------|----------------|--------|
| Wire Size | 14 - 10 AWG | Indoor/Outdoor | Indoor |
|-----------|-------------|----------------|--------|

| | | | |
|---------|---------|--------------------------|-----------------------|
| Voltage | 125.0 V | Environmental Conditions | Flammability: UL94 V2 |
|---------|---------|--------------------------|-----------------------|
