



Hospital Grade Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). Back and Side Wire, 20A, 125V, Blue.

## Features & Benefits

<p>Solid-state LED monitor has 25-year minimum life expectancy. A high visibility, wide-angle lens indicates protection is in place.</p>	<p>One-piece brass, triple-wipe power contacts for lasting retention.</p>
<p>Audible alarm alert of MOV damage. Alarm able to be turned On/Off.</p>	<p>Wrap-around steel strap for structural integrity. Auto-ground is standard, for easier installation.</p>
<p>Impact-resistant thermoplastic exterior resists impacts and scrapes.</p>	<p>Triple-wipe, copper-alloy contacts for superior, more dependable connection.</p>
<p>Thermal protection in 3 modes. 3 17mm dual pack MOVs absorb up to 340 Joules of excess energy in each leg (L-N, L-G, N-G) with 24,000 amp current handling capability for full, equal and symmetrical protection. Protection response time in less than one nanosecond.</p>	<p>For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a>.</p>

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brown
Country Of Origin	Mexico	Application Sector	Commercial
Standard	cUL UL1449, UL498: CSA C22.2 No. 42: ANSI/IEEE C62.41 (Formerly IEEE 587), ANSI/IEEE C62.45 Installation Categories "A" (Ring Wave) "B" (Unidirectional Impulse).		

### Dimensions

Product Width US	1.75 in	Product Depth US	1.225 in
------------------	---------	------------------	----------

---

Product Height US	2.8 in
-------------------	--------

---

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

---

### Technical Information

---

Connection	Back and side wire	Class	IG
------------	--------------------	-------	----

---

Amperage	20 A	Voltage	125.0 V
----------	------	---------	---------

---

Environmental Conditions	Flammability: UL94 V2
--------------------------	-----------------------

---