



Wiremold  
880W Series™ Two Gang Steel Floor Box for Wood Floors  
Part No. 880W2



The 880W2 two gang Omnibox® Floor Box provides an excellent activation solution for applications where single service is required in open space areas. The 880W2 floor box is offered in a stamped steel construction, designed to be installed in wood floor applications and to meet a wide range of market requirements. This floor box series has many applications, some of which are schools, financial institutions, and commercial office buildings.

## Features & Benefits

The 880W2 two gang Omnibox® Floor Box provides an excellent activation solution for applications where single service is required in open space areas.

This floor box series has many applications, some of which are schools, financial institutions, and commercial office buildings.

The 880W2 floor box is offered in a stamped steel construction, designed to be installed in wood floor applications and to meet a wide range of market requirements.

## Specifications

### General Info

Product Line	Wiremold	Color	Silver
UPC Number	786564109570	Country Of Origin	Mexico
Construction	Assembled	Cover Style	Surface
Cover Material	Brass	Application Sector	Commercial
Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT. Meets Article 314.27(C) of NEC.	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Floor Box		

### Dimensions

Product Width US	5.0 in	Product Weight US	4.09 lb
------------------	--------	-------------------	---------

Product Volume US	150.94 cu in	Product Depth US	8.63 in
Product Height US	3.5 in	Cubic Capacity	117 in³
Knockout Size	1 in, 1/2 in, 3/4 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E2961	cULus Listed	Yes
Trade Programs			
USMCA	Yes		
Additional Information			
RoHS Compliant	Yes	Product Environmental Profile	Yes
Technical Information			
Floor Type	Carpet, Tile, Wood	Service Capacity	Dual
Box Capacity	2 Gangs	Cable Entry	knockout
Number of Outlets	0	Depth Behind Device Plates	2.75 in