



Perfect for anywhere you'd like the combined power of on/off and dimmable lighting control. Turn lights on or off with a simple rocking motion, or slide to dim to your preferred light level. Use this dimmer switch on its own to control a CFL or LED light or fixture from a single location, or pair with a 3-way switch to control a single light source from two locations.

This dimmer\* features enduring Microban Registered antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

\* Existing inventory of switches, dimmers and plastic wall plates from the adorne Registered Collection at some partner locations may not yet include Microban Registered protection. To confirm that a specific Legrand product is protected with Microban Registered, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne Registered Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

## Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

For use with dimmable CFL/LED bulbs or fixtures. Features smooth paddle action for turning lights on and off, plus easy slider for adjusting lights to your preferred light level.

Usable in both single-pole and 3-way applications.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

## Specifications

### General Info

Product Line	Pass & Seymour	Replaced by Part Number	ADPD153LG2
Color	Graphite	Finish	Metallic
UPC Number	785007233858	Country Of Origin	China
Material	Polycarbonate	Features	Antimicrobial Protection, Locator Light, Low-End Trim (Dim Range)
Switch Type	Paddle, Slider	Number of Switches	1

Application Sector	Residential	Warranty Type	Limited Lifetime Warranty
Type	Dimmer		
<b>Dimensions</b>			
Product Width US	1.77 in	Product Depth US	1.62 in
Product Height US	4.2 in		
<b>Technical Information</b>			
Load Rating	120V 450W (CFL), 120V 450W (LED), 120V 600W (Halogen), 120V 600W (Incandescent)	Dimming Compatibility	Forward Phase
Frequency Rating	60 Hz	Number of Poles	Single Pole 3-Way
Wire Size	#14 - #10 AWG	Requires Neutral Wire	No
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Screw Terminals	Voltage	120 VAC
Load Type	CFL, Halogen, Incandescent, LED		