



□

Hospital Grade AFCI/GFCI specially designed and tested for rigorous healthcare applications.

Features & Benefits

Separate indicator lights on the Dual-Function AFCI/GFCI Receptacles for AFCI Hospital Grade AFCI/GFCI specially designed and tested for rigorous healthcare applications and GFCI make it easy to distinguish between a trip caused by an arc fault and a ground fault

Separate indicator lights on the Dual-Function AFCI/GFCI Receptacles for AFCI Two back-wire holes per termination add and GFCI make it easy to distinguish between a trip caused by an arc fault and a wiring flexibility, eliminate pigtail and save ground fault box space

High-impact-resistant, thermoplastic construction for superior strength and durability Ground terminal back-wire for fast installation

Two indicator lights, one for GFCI and one for AFCI. Easy to distinguish between trip caused by arc fault and trip caused by ground fault. GFCI indicator light flashes if device fails the self-test, signaling that the AFCI/ GFCI receptacle should be replaced Auto-ground clip assures a positive ground to metal box

Part of the radiant® collection of wiring devices and wall plates FSUL Listed (Federal Specification WC596)

Feed-through protection Patented SafeLock® Protection—if critical components are damaged and ground fault protection is lost, power to the receptacle is disconnected

Prevents line-load miswire—no power to the face or downstream receptacles if wired incorrectly

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007271140
Country Of Origin	China	Number of Receptacles	2
Outlet Type	AFCI, GFCI, Tamper-Resistant	Application Sector	Commercial, Hospital Grade
Type	AFCI, Duplex, GFCI, Tamper-Resistant		

Additional Information

RoHS Compliant Yes

Technical Information

Is Tamper-Resistant Yes

Number of Gangs 1

Amperage 20 A

Is Weather Resistant No

Indoor/Outdoor Indoor

Mounting Type Box

Voltage 125.0 V
