



Add contemporary style, safely, to kitchens, bathrooms and more, with GFCI Outlets from the adorne Collection. Meeting Electrical Code* for ground fault protection in the home, GFCI outlets make it easier to fix trips right where they happen – no more confusion or running to the breaker box. The adorne GFCI Outlets also self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. *GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Conducts an industry-leading automatic self-test every 3 seconds. If the device ever fails, the indicator light flashes to signal it should be replaced.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Protects against shock caused by ground-fault occurrences. Unlike breaker alternatives, GFCI outlets make it easier to fix trips with a convenient reset button on the outlet.

Configuration easily supports two plugs and offers the capacity of a standard 15A outlet, in a uniquely contemporary design.

Replaces any standard outlet with ease, in as little as 10 minutes.

Specifications

General Info

| | | | |
|-----------------------|---------------------------|-------------------|--------------------------------------------------------|
| Product Line | Pass & Seymour | Color | Magnesium |
| Finish | Frosted | Country Of Origin | China |
| Number of Receptacles | 2 | Outlet Type | GFCI, Indoor, Residential, Self-Test, Tamper-Resistant |
| Application Sector | Residential | Standard | CULUS |
| Warranty Type | Limited Lifetime Warranty | Type | Outlet |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 1.82 in | Product Depth US | 1.77 in |
| Product Height US | 2.66 in | | |

Technical Information

| | | | |
|--------------------------|-----------------------------------------|------------------|--------------------------|
| Is Tamper-Resistant | Yes | Interrupt Rating | 15 A |
| Phase | Single | Frequency Rating | 60 Hz |
| Trip Range | 4 to 6 mA | Connection | Side & Back Wire |
| Number of Gangs | 1 | Amperage | 15 A |
| Number of Poles | Double Pole | Indoor/Outdoor | Indoor |
| NEMA Configuration Code | 5-15R | Mounting Type | Box |
| Voltage | 125 V | Connection Type | Internal Pressure Plates |
| Environmental Conditions | 95% (relative humidity, non-condensing) | | |