



Approved Networks

Juniper JNP-QSFP-100G-SR4 Compatible 100GBase-SR4 QSFP28 Transceiver (MMF, 850nm, 100m, MPO/MTP, DDM, C-Temp)

Part No. JNPQSFP-100G-SR4-A

- Juniper JNP-QSFP-100G-SR4 Compatible 100GBase-SR4 QSFP28 Transceiver (MMF, 850nm, 100m, MPO/MTP, DDM, C-Temp)

Features & Benefits

Guaranteed Compatible: In System tested in over 90 OEM switches, routers and servers.

99.98% Reliability Rate: Functionally, optically and environmentally tested to exact specifications.

Industry Leading Lifetime Warranty: For more information by product line, visit our Warranty page.

98% On-Time Delivery Rate: Extensive inventory guarantees same day shipping.

Full Service Technical Support: Call, chat, email or meet for expert optical connectivity support.

Specifications

General Info

Product Line	Approved Networks	Color	Silver
Country Of Origin	China	OEM Manufacturer	Juniper
Features	Digital Diagnostic Monitoring, Digital Optical Monitoring	Application Sector	Commercial, Data Center, Industrial
Standard	IEEE 802.3bm;SFF-8636;CAUI-4	Warranty Type	Lifetime
Type	Transceiver		

Dimensions

Product Width US	18.8 mm	Product Weight US	0.4 oz
Product Depth US	123.21 mm	Product Height US	11.68 mm

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Fiber Optic Cable Type	Multimode	Max Distance Support	150 m
Operating Temperature Min	0 °C	Transceiver Type	VCSEL
TX Power Min	-8.4 dBm	Protocol	Ethernet
Operating Temperature Max	70 °C	Media Type	Fiber
RX Sensitivity	-9.5 dBm	Data Transfer Rate	42 Gbps
TX Power Max	2.4 dBm	Connector Type	MPO
Wavelength	850 nm	Form Factor	QSFP+

Operating Temperature 0°-70°C
